

Dental instrument Benchtop Ultrasonic Cleaner Large Capacity CE RoHs

Basic Information

- Place of Origin:
- Brand Name:
- Certification:
- Model Number:
- Minimum Order Quantity:
- Price:
- Packaging Details:
- Delivery Time:
- Payment Terms: L/
- Supply Ability:
- Supply Ability.



- carton box 410*255*310mm
- In Stock
- L/C, T/T,Paypal

China

Skymen

500 sets per week



Product Specification

- Clean Medium:
- Automation:
- Control Mode:
- Theory:
- Status:
- Character:
- Δ١
- Customize:Highlight:
- Semi Automatic Artificial Physical Cleaning New High Efficiency Available

Wet Cleaning

skymen ultrasonic cleaner, stainless steel ultrasonic cleaner



More Images



Dental instrument Benchtop Ultrasonic Cleaner Large Capacity CE RoHs

Specifications:

Model	JP-030S
Ultrasonic power	90/180W (3pc transducer)
Frequency	40KHz
Housing material	SUS304
Tank material	SUS304
Heating power	200W
Tank capacity	4.5 L
Timer	Digital 1-30min adjustable
Heater	20~80°C
Voltage	AC 100~120V, 60Hz AC 220~240V, 50Hz
Tank size	300*150*100 mm
Unit size	325*180*225 mm
Packing size	410*255*310mm
N.W.	4.6 Kg
G.W.	5.4 Kg
Certificate	RoHs / CE

How does ultrasonic cleaning work?

Specially designed transducers transform electric energy into mechanical vibrations. These are transmitted into the cleaning liquid, creating many tiny vacuum-filled bubbles which rapidly implode. This process, called cavitation, releases highly energetic jets of liquid which remove all kinds of contamination from metal, glass, and plastic surfaces. Every surface that comes in contact with the fluid is thoroughly cleaned.



